

SATWIPESTM Wipes (IPA)

Presaturated 100% lyocell (rayon) wipes with isopropyl alcohol

SATWIPESTM with 8642 aerospace fabric consists of a roll of saturated wipes dispensed through a reusable center-pull canister with a self-closing lid. The wipes are 100% lyocell (rayon) fabric that is hydraulically entangled, creating a soft, durable, and clean wipe that provides safe, consistent solvent application and use. Presaturation eliminates the need for solvent bottles, reduces solvent handling and solvent use by up to 35%, and improves the consistency of wipe wetness, which allows for a more uniform distribution of solvent.

SATWIPESTM are tailored to specific tasks in your facility. This ensures that the right size wipe with the correct amount of solvent is used each time. Durable reusable canister with self-closing lid reduces waste, solvent use and VOCs. *Meets current revision of specification AMS3819.*



Features	Benefits
Solvent specific color-coded labeling	• Easy solvent identification
Perforated rolls with self-closing lids	• Lids close to prevent wipes from drying out
Reusable canister	• Economical and solvent compatible
Various solvent blends	• Meet different facility needs
Rayon/nonwoven fabric	• Meets aerospace specification AMS3819

Part No.	Description	Size	Packaging	Canister Part No.
SW420951	SATWIPESTM Wipes Presaturated with 70% USP IPA/30% DI water, 442 ml	4" x 4.25" (102 x 108 mm)	200/roll; 12 rolls/case	SWCN1082
SW420284	SATWIPESTM Wipes Presaturated with 99% USP IPA/1% DI water, 800 ml	6" x 5.83" (150 x 148 mm)	150/roll; 12 rolls/case	SWCN0284
SW250054	SATWIPESTM Wipes Presaturated with 100% USP IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 18 rolls/case	SWCN0089
SW250089	SATWIPESTM Wipes Presaturated with 100% USP IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 12 rolls/case	SWCN0089
SW252010	SATWIPESTM Wipes Presaturated with 100% USP IPA, 700 ml	6" x 9" (150 x 230 mm)	100/roll; 6 rolls/case	SWCN0089
SW420003	SATWIPESTM Wipes Presaturated with 100% USP IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 12 rolls/case	SWCN0089
SW420009	SATWIPESTM Wipes Presaturated with 85% USP IPA/15% DI water, 889 ml	6" x 9" (150 x 230 mm)	100/roll 18 rolls/case	SWCN0089
SW420011	SATWIPESTM Wipes Presaturated with 100% USP IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 12 rolls/case	SWCN0089
SW420077	SATWIPESTM Wipes Presaturated with 100% SEMI IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 18 rolls/case	SWCN0089

Part No.	Description	Size	Packaging	Canister Part No.
SW420139	SATWIPES Wipes Presaturated with 100% USP IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 18 rolls/case	SWCN0155
SW420146	SATWIPES Wipes Presaturated with 100% USP IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 12 rolls/case	SWCN0146
SW420181	SATWIPES Wipes Presaturated with 100% USP IPA, 870 ml	6" x 9" (150 x 230 mm)	100/roll; 18 rolls/case	SWCN0089
SW420195	SATWIPES Wipes Presaturated with 100% USP IPA, 800 ml	6" x 9" (150 x 230 mm)	100/roll; 18 rolls/case	SWCN0089
SW420250	SATWIPES Wipes Presaturated with 70% USP IPA/30% DI water, 889 ml	6" x 9" (150 x 230 mm)	100/roll; 18 rolls/case	SWCN0250
SW250053	SATWIPES Wipes Presaturated with 100% USP IPA, 1,200 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0044
SW420034	SATWIPES Wipes Presaturated with 100% USP IPA, 1,100 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0224
SW420038	SATWIPES Wipes Presaturated with 100% USP IPA, 1,200 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0044
SW420044	SATWIPES Wipes Presaturated with 100% USP IPA, 1,200 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0044
SW420078	SATWIPES Wipes Presaturated with 100% SEMI IPA, 1,200 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN1040
SW420132	SATWIPES Wipes Presaturated with 90% USP IPA/10% DI water, 1,178 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0132
SW420138	SATWIPES Wipes Presaturated with 100% USP IPA, 1,200 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0044
SW420147	SATWIPES Wipes Presaturated with 100% USP IPA, 1,200 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0044
SW420941	SATWIPES Wipes Presaturated with 50% USP IPA/50% DI water, 1,165 ml	9" x 11" (230 x 280 mm)	75/roll; 6 rolls/case	SWCN0044
SW420981	SATWIPES Wipes Presaturated with 85% USP IPA/15% DI water, 1,200 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0044
SW420996	SATWIPES Wipes Presaturated with 70% USP IPA/30% DI water, 800 ml	9" x 11" (230 x 280 mm)	75/roll; 12 rolls/case	SWCN0996
SW250024	SATWIPES Wipes Presaturated with 100% USP IPA, 800 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0011
SW250124	SATWIPES Wipes Presaturated with 50% SEMI IPA/50% DI water, 1,171 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0124
SW420051	SATWIPES Wipes Presaturated with 100% USP IPA, 1,400 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0044
SW420066	SATWIPES Wipes Presaturated with 100% USP IPA, 1,400 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0044
SW420129	SATWIPES Wipes Presaturated with 100% USP IPA, 1,400 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0044
SW420137	SATWIPES Wipes Presaturated with 100% USP IPA, 1400 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0044
SW420145	SATWIPES Wipes Presaturated with 100% USP IPA, 1,400 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0044
SW420173	SATWIPES Wipes Presaturated with 100% USP IPA, 1,200 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0044
SW420946	SATWIPES Wipes Presaturated with 70% USP IPA/30% DI water, 1,186 ml	11" x 17" (280 x 430 mm)	50/roll; 12 rolls/case	SWCN0946

Product Information	
Material	100% lyocell (rayon)
Construction	Hydroentangled nonwoven

Technical Data		
Attribute (units)	Typical Value	Test Method
Basis weight, nominal; (g/m²)	66	
Non-volatile residue, NVR		IENT-RP-CC004.2, Sec. 6.1.2
In deionized water; (g/m²)	0.014	
In isopropyl alcohol; (g/m²)	0.027	
Specific ions		IENT-RP-CC004.2, Sec. 6.2.2
Sodium; (ppm)	<10	
Chloride; (ppm)	<10	
Particles, readily releasable		IENT-RP-CC004.2, Sec. 5.1
Particles ≥ 3.0µm; (x10⁶/m²)	15.0	
Fibers ≥ 100µm; (x 10³/m²)	55	IENT-RP-CC004.2, Sec. 5.2



Contec standard canisters are made of High Density Polyethylene (HDPE) and are both reusable and recyclable. These canisters have been proven to withstand contact with the harshest of solvents. The triple threading ensures that the lid (when screwed on properly) will stay on the canister. The variety of lids choices ensures that there is a lid to respond to every need.

Canister Part No.	Diameter	Height
SWCN0044	4 15/16"	11 7/8"
SWCN0089	4 15/16"	7 3/8"

Recycle Symbol

HDPE



- Notes
- a) The data shown are typical values and should not be used as product specifications.
 - b) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
 - c) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Part No.	VOC Content pounds/pouch	VOC Content pounds/case
SW420951	0.61	7.27
SW420284	1.39	16.68
SW250054	2.08	25.02
SW250089	1.39	16.68
SW252010	1.22	7.3
SW420003	1.39	16.68
SW420011	1.39	25.02
SW420077	2.13	25.56
SW420139	2.66	31.94
SW420146	1.39	16.68
SW420181	1.51	27.2
SW420195	1.39	25.02
SW420250	1.21	21.8
SW250053	2.08	25.02
SW420034	1.91	22.93
SW420038	2.08	25.02
SW420044	2.08	25.02
SW420078	2.05	24.57
SW420132	1.91	22.89
SW420138	2.08	25.02
SW420147	2.08	25.02
SW420941	1.02	6.15
SW420981	1.88	22.5
SW420996	1.54	18.46
SW250024	2.08	25.02
SW250124	1.21	14.57
SW420051	2.43	29.19
SW420066	2.43	29.19

Part No.	VOC Content pounds/pouch	VOC Content pounds/case
SW420129	2.43	29.19
SW420137	2.43	29.19
SW420145	2.43	29.19
SW420173	2.08	25.02
SW420946	1.59	19.14