



QuickTurn™ Mop

Lightweight floor mop with 32 oz. solution tank

When time, convenience, and clinical effectiveness matter, turn to Contec's QuickTurn™ reservoir mop. Ideal for cleaning and disinfecting between large areas, this economical thermoplastic and aluminum mop is lightweight and easy to use, reducing time and operator fatigue. Its 32 ounce dispensing tank is removable for easy filling and cleanout. Eliminates extra steps, extra water and extra chemical wasted in traditional mop and bucket systems.

Designed for use with Contec Professional's Premira® Microfiber Pads for added convenience, speed, and efficiency. A must have for faster turnovers in procedure and patient areas. For floor use only.

FEATURES

- Reservoir system simplifies and speeds cleanup between cases
- One-step mopping process eliminates the hassle of heavy mop buckets and increasing operating efficiency
- Controlled release trigger, press to dispense chemical, press again to stop dispensing, extending the useful life of the floor pads


Contec part no.	description	size	packaging
ATFM0001	QuickTurn™ Mop with 32 oz. tank, ZeroGravity™ frame and adapter		1/mop, 1/frame, 1/adapter
2781	QuickTurn™ Mop with with 32 oz. tank	55" (140 cm)	1/each
PRMM0001	Premira® II Microfiber Pad, 5" x 19"	5 x 19" (13 x 48 cm)	20 pads/bundle, 12 bundles/case
PRMM3001	Premira® Microfiber High Sorbency Microfiber Pad	5 x 19" (13 x 48 cm)	36 pads/case
PRMH8005	ZeroGravity™ Mop Frame, blue	17.5" (44 x 5 cm)	6 frames/case
PRMH1006	Adapter, QuickTurn™ to ZeroGravity™ frame	9.75" (25 cm)	1/each
2705	QuickTurn™ Mop Tank with orange cap, 32 oz, replacement part	32 oz.	1/each



ZeroGravity™ Mop Frame

Even and consistent cleaning

Paired with our Premira mops, this lightweight tool is semi-disposable and 100% recyclable, eliminating the risk of contaminated, nasty looking hardware. The ZeroGravity mop frame ensures that the mop pad is applied to the floor with consistent pressure for even cleaning and uniform application of disinfectant, which allows dwell times to be properly achieved.



ContecProfessional.com