

# Contec® MicroCinch™ Mop

## Microfiber flat mop

The USP <797> compliant, disposable Contec MicroCinch Mop is constructed with 100% synthetic microfiber that provides superior removal of gross soil and fine particulate. Reduces cross contamination associated with reprocessed mops, and is suitable for ISO Class 7 and 8 environments. Compatible with most common disinfectant chemistries including quaternary, alcohol, peroxide, and bleach-based disinfectants, the low-lint flat mop can be used wet or dry, and the pad provides uniform surface coverage and liquid distribution.

The “pocket” style design allows for quick changing of mop pads and the collapsible mop frame, available in heavy-duty plastic, easily snaps into the pad pockets. Contec’s MicroCinch Mop is the ideal solution for daily cleaning and disinfecting of Secondary Engineering Controls required in pharmacy environments. Cleanroom packaged for guaranteed quality and cost effectiveness.

Mops are available sterile per AAMI guidelines.



Part No.	Description	Size	Packaging
HCPM5001	EasyReach Cleaning Pads, quilted polyester	5" x 15.5" (13 x 39 cm)	8/bag; 15 bags/case
HCPM5051	EasyReach Sterile Cleaning Pads, quilted polyester	5" x 15.5" (13 x 39 cm)	2/bag; 35 bags/case

Technical Data		
Attribute (units)	Typical Value	Test Method
Mop weight, dry; (g/mop)	16	Contec Method
Sorbent capacity; (mL/mop)	182	CTM004-03
Non-volatile residue, NVR		IEST-RP-CC004.2, Sec. 6.1.2
In deionized water; (g/mop)	0.01	
In isopropyl alcohol; (g/mop)	0.01	
Particles, P ≥ 0.5µm; (x10 <sup>6</sup> /mop)	50.14	IEST-RP-CC004.2, Sec. 5.2
Fibers ≥ 100µm; (x 10 <sup>3</sup> /mop)	0.16	IEST-RP-CC004.2, Sec. 5.2

Product Information	
Material	<ul style="list-style-type: none"> <li>• Polyester microfiber; polyester and polypropylene</li> </ul>
Construction	<ul style="list-style-type: none"> <li>• Multilayer stitched lamination</li> </ul>

- Notes:**
1. The information presented here is applicable to the part numbers shown above, as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
  2. Data shown are typical values and should not be used as product specifications.
  3. Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
  4. Current and/or comparison data may be available. Please contact a Contec sales representative for details.

TDS002HC | 122122

Copyright © 2022 Contec, Inc. All rights reserved.